## **Datasheet**

**ABA128 Optical Encoder System** 



## **Highlights**

- Miniature optical absolute encoder, suitable for confined spaces
- Compatible with linear and rotary measurement, user-programmable 22-bit to 26-bit
   resolution for different precision requirements
- Real-time signal monitoring and debugging via the Encoder Test Box (ETB)
- **BiSS C** or **BiSS C + 1 Vpp** dual output options
- High-speed performance: up to 10 m/s linear, 3800 rpm rotary
- Auto Gain Control (AGC) to maintain optimal signal quality
- Auto Offset Calibration (AOC) for easy position optimization
- Auto Accuracy Calibration (AAC) to enhance system accuracy
- Compatible with soda-lime glass scales, steel tapes, and discs
- Excellent electromagnetic interference (EMI) resistance
- Multi-color LED indicators for intuitive signal status display

**Optical Readhead** 

1. Specifications

Specification			Optical Readhead	
Image			Wecho Committee of the	
Series			ABA128-B	ABA128-BA
Description			Miniature readhead, suitable for both linear and rotary motion,	
Description				optical encoding
Scanning Princip	le		1	Reflective)
Scanning Type			solute	
Signal Period		128 μm		
Output Signal		T	BiSS C	BiSS C + SinCos 1Vpp
	BiSS C Linear Motion Rotary Motion		0.2 μm   0.1 μm   0.05 μm	
Resolution		Rotary Motion	22-bit to 26-bit (Single turn) <sup>1</sup>	
Resolution	SinCos 1Vpp		Not Supported	Depends on the driver's interpolation factor
Power Supply (Without Load)	4.5 VDC to 5.5 VDC		<80 mA	(Typical)
Temperature	Storage		-20 °C to +70 °C @ RH < 80% (Non-condensing)	
	Operating		0 °C to +70 °C @ RH < 80% (Non-condensing)	
Acceleration	Operating		500 m/s <sup>2</sup> , 3 Axes	
Shock	Non-Operating		<1000 m/s², 6 ms, ½ Sine, 3 Axes	
Vibration	Operating		<100 m/s <sup>2</sup> Max @ 55 to 2000 Hz, 3 Axes	
Mass	Readhead		5.5 g	
	Cable			g/m
Cable Design		BiSS C	8 Cores, Double Shielded	10 Cores, Double Shielded
Cable Diameter		3.5±0.2 mm		
Cable Bend	Static		30 mm	
Radius Dynamic		70 mm  DSUB 15 Male		
Cable Termination		Langth	20.57 mm	
Readhead	Length Width		20.37 mm 12.70 mm	
Dimension			10.50 mm	
IP Rating	Height Height		IP40	
IP Rating Note:		1P40		

<sup>1.</sup> For rotary motion applications requiring readheads with higher data resolution, please contact our sales team for more information.

# 2. Speed Performance 2.1 Linear Motion

Max Speed (m/s)	
10	


## 2.2 Rotary Motion

Lines per Revolution, LPR	Outer Diameter (mm)	Inner Diameter (mm)	Max Speed (RPM)
1250	55.00	41.00	3800
1650	70.00	56.00	2890
2048	86.20	70.00	2300
2500	106.00	90.00	1890
3125	131.40	113.00	1500
4096	171.20	153.20	1150
5000	206.40	188.40	940

## 3. LED Definition

Model	ABA128
LED Location	On readhead body  LED  Wecho  ABA128  C €
LED Colour Green	Powered on


4. Readhead Dimension Drawing




- 1. All dimensions are in mm.
- 2. Mount the readhead using two holes, such as (I) (II) or (II) (III)

## 5. Readhead Installation Guide

During installation, please strictly follow or refer to the diagrams below to ensure accuracy and consistency. Pay close attention to the cable exit direction, as well as the definitions and labels of yaw, pitch, and roll. Proper understanding and application of these orientations are critical for precise assembly, calibration and future operation.




5.1 Soda-lime Scale with Adhesive (SA128-G8)



#### Note:

- 1. All dimensions are in mm.
- 2. SL = Scale length
- 3. ML = Measuring length

5.2 Stainless Steel Scale with Adhesive (SA128-SS)




- 1. All dimensions are in mm.
- 2. SL = Scale length
- 3. ML = Measuring length
- 4. T = Beginning of the measuring length

#### 5.3 Soda-lime Disc without Adhesive (RA128-G8N)


For customization of glass discs, please contact our sales team for more information.

5.4 Stainless Steel Disc without Adhesive (RA128-SSN)



- 1. All dimensions are in mm.
- 2. T = Datum T
- 3. Use UV glue for installation, do not use 502 glue.

## 6. Electrical Connection




**IMPORTANT:** Readhead shield must be connected to the driver earth (Field ground).


Maximum readhead cable length: 5 m

#### 7. Pinout

7.1 BiSS C Output Signal




7.2 BiSS C + SinCos 1Vpp Output Signal



## 8. Communication Protocol

#### 8.1 BiSS C

## 8.1.1 Single Cycle Data (SCD) Format Latch position



8.1.2 Timing Specifications


Communication Protocol		
Type of interface	BiSS C, point to point	
Signal level	RS485	
Master clock (MA) frequency	See table below	
Length of position data	27-bit	
Length of status data	2-bit (Error and warning, active LOW)	
Length of cyclic redundancy check (CRC)	6-bit (Polynomial 0×43, transmitted inverted)	
Position data encoding	Binary	
Latency time	5.5μs (at 10MHz)	
Recovery time	≥ 300ns	
Request cycle rate	90 kHz (at 10MHz)	

8.1.3 Master Clock (MA) Frequency

Frequency, MHz*	OK
0.5	√
1.0	$\sqrt{}$
2.0	√ (Typical)
2.5	√ (Typical)
5.0	$\checkmark$
10.0	(For cable length $\leq 0.2 \text{ m}$ )

<sup>\*</sup> BiSS is a trade mark of ic-Haus GmbH, who tested and specified all these frequencies

### 9. Model Name



#### Note:

1. For customization, please contact our sales team for more information.

## 10. Compatible Scale/Disc

00222002020	~ ~ · · · · · · · · · · · · · · · · · ·	
Type	Model	Description
Caala	SA128-G8	Linear absolute 128 µm grating period, soda-lime glass with adhesive
Scale	SA128-SS	Linear absolute 128 µm grating period, stainless steel with adhesive
Disc	RA128-G8N	For customization, please contact our sales team for more information
	RA128-SSN	Rotary absolute 128 µm grating period, stainless steel without adhesive

## 11. Accessories List

Part Number	Image	Description
N/A	0.80 mm	<b>0.80 mm Shim Kit</b> is used during readhead assembly to precisely adjust the rideheight between the readhead and the scale, ensuring optimal signal quality. By using the appropriate shims, the required rideheight can be accurately achieved, preventing signal degradation and enhancing the overall performance of the readhead.  * Included in every readhead